


Ecolift XL backwater lifting st. Duo, 2 motor-driven flaps, SPF 4500-S1





Article information

Item no.: 8741037 GTIN: 4026092068540 Price group: 60

Advantages

- Wastewater drainage without interruption, even if a power failure occurs, as long as there is no backwater
- low pump use
- minimised noise emissions

Description

The backwater lifting station for faecal and non-faecal wastewater is equipped with two submersible pumps, two motor-driven closure systems and a backflow preventer. The collection tank made of permanently resistant polymer (PE) has an enclosed pump tank. Quick-release closures enable the integrated components to be removed easily. The pipe cross-section is normally open and the water drains to the sewer via natural fall. Backwater is detected by an optical probe, which causes the closure systems to close automatically and there is no longer free passage to the sewer. During the backwater phase, the water drains via a pressure pipe, which carries the wastewater into the sewer. The pressure pipe is a welded PE pipe; with pump SPF 4500, the pressure pipe must also be continued up to a pressure release chamber. The station is controlled by a user-friendly control unit, which is optionally integrated in the building management system via a potential-free contact, or alarm and collective fault messages can be output via a GSM interface. A redundant control unit also provides additional safety. The KESSEL modular system provides different upper sections and engineering chamber options as accessories.

Variant Note on installation depth: Type of system: Shut-off valve:

Version for deeper installation duo pump Shut-off valve made of polymer



Passage seal for conduit pipe (DN): Passage seal for ventilation pipe (DN): Rim width: Backwater protection: Pressure pipe connection: Motor-driven backwater flaps:	100 70 Control unit integrated horizontal 2
General characteristics Colour: Standard: Type of wastewater: Installation situation: Delivery state: Backwater protection: Inlet max. scoring (DN):	black ÖNORM B 2501 for wastewater with and without sewage free-standing installation Pre-mounted for final assembly on site (pumps and sensor system must be fitted on site and control unit must be connected) Type 6 Z-53.2-493
Dimensions Net weight: Gross weight: Groundwater resistant from lower edge of base section: Vertical drop between inlet and outlet: Width: Height: Length: Packaging dimension: Packaging dimension: Packaging dimension:	156 kg 177,07 kg 3000 mm 15 mm 1200 mm 695 mm 1384 mm width height length
Tank/drain body Nominal pressure (PN): Pressure pipe connection (DN): Pressure pipe connection (OD): Channel: Venting connection (DN): Distance pipe bottom outlet to tank bottom: Distance pipe bottom inlet to tank bottom: Number of outlets: Outlet nominal size (DN): Inlet nominal size (DN): Inlet type: Clear width of tank (LW): Pumping volume: Tank volume:	10 80 90 mm continuous channel 70 120 mm 135 mm 1 150 150 1 1000 mm 20 l 65 l
Pumping device Pump control: Number of pumps:	SPF 4500 2



Weight: Connection type: Rated current: Length of mains cable for pump: Self-diagnosis system (SDS): L F Insulation class: Cos phi - power factor: Protection class control unit: DSC: Max. temperature (permanent) of conveyed material: Max. pumping capacity: Max. pumping height: Speed: Power P1: Power P2: Operating mode: S1 Type of fuse required (electrical protection): Type of pump connection cable: Impeller type: Free passage: Control Motor protection switch: Standby power: Alarm sensor: Level measurement instrument: Type of level measurement: Protection class probe: Operating voltage:

31 kg Direct connection 7.5 A 10 m 0,88 IP 68 (3m/48h) integrated 40 °C 45 m³/h 21 m 2850 U/min 4.2 kW 3,5 kW 3 x C 25 A H07RN-F 7G 1.5 mm² Multi-vane impeller 40 mm yes 5 W optical probe Immersion pipe pneumatic IP 54 400 V **Direct connection** yes yes yes yes yes yes yes Comfort Plus with redundancy

Connection type:

GSM interface:

USB interface:

Log book function:

Multi-line display:

Battery buffering:

Self-diagnosis system (SDS):

Max. permissible switching frequency:

Potential-free contact: